

The FUNDA family of filter can be ordered with many accessories. Any accessory that your process requires can be designed in, right from the start. Additional spare nozzles can be added for later use to accommodate temperature probes or other components should the need arise in the future.



*Purged Motor Cover*

### Motor Cover


In sterile environments a purged motor protection cover can be installed. It provides a smooth, clean appearance and may be ordered with windows for observing gearbox oil levels.



*Automatic Valves  
Instrumentation  
Transmitters & Gauges*

### Protection Guard

For personnel protection from rotating components, metal guards are available for the motor support openings.



*Protection Guard*



*Explosion Proofed Pre-coat Pump*

### Process Pumps

Steri has the experience and know to select and supply fluid handling pumps that are best suited the application. Proper flow rates and pressure control are essential for maximum filtration performance.

### Bag Loading

Your process may need the addition of filter aid during the filtration step. You can take advantage of the decades of experience Steri has accumulated by having us design a pre-coat or body feed dosing system tailored for your process.



*Bag Loading Station*



*Nest Assembly Platform*



*Load Cell*

### Load Cells

Load cells can be installed to measure the amount of cake as it builds on the filter plates. This insures the filter will not become overloaded and can assist when performing a cake discharge to verify all cake has been removed.